



**THE OPTICAL PROPERTIES OF  
A GERSHWIN PTY LTD BLACK MESH SCREEN SAMPLE**

**M.G. Hutchins**

**Solar Energy Materials Research Laboratory  
Sonnergy Limited**

**Report No. 10/334**

**May 2010**

**THE OPTICAL PROPERTIES OF A GERSHWIN PTY LTD  
BLACK MESH SCREEN SAMPLE**

**Contents**

1.	Introduction	1
2.	The Gershwin Pty Ltd Sample	2
3.	Experimental procedures	2
3.1.	Measurement of Spectral Transmittance and Reflectance	2
4.	Calculation Methods	4
4.1.	Visible transmittance and reflectance	4
4.2.	Solar transmittance and reflectance.	4
4.3.	Ultraviolet Transmittance	5
4.4.	Total solar energy transmittance, shading coefficient and shading factor	6
5.	Results	8
6.	References	13

## I. List of Tables

Table 1.	Identification of the Gershwin Pty Ltd sample.	2
Table 2.	Values of the glazing thermal transmittance, U, and total solar energy transmittance, g, used to calculate the $g_{total}$ and shading coefficient values for the blind fabrics placed internally (taken from EN 14501 (10)).	7
Table 3.	Values of the glazing thermal transmittance, U, and total solar energy transmittance, g, used to calculate the $g_{total}$ and shading coefficient values for the blind fabrics placed internally (taken from EN-13363-1 (11)).	7
Table 4.	Integrated total near-normal hemispherical solar, visible and ultraviolet optical properties of the Gershwin Pty Ltd black mesh screen sample.	10
Table 5.	Integrated total near-normal hemispherical, near-normal diffuse and normal-direct solar and visible transmittance of the Gershwin Pty Ltd black mesh screen sample.	10
Table 6.	Integrated total near-normal hemispherical, near-normal diffuse and normal-direct solar and visible reflectance of the Gershwin Pty Ltd black mesh screen sample.	10
Table 7.	Calculated total solar energy transmittance, $g_{total}$ , shading coefficient, (SC), and shading factor, $F_c$ , values of the Gershwin Pty Ltd black mesh screen sample used as external shading in combination with the four standard glazings of EN 14501 (10).	11
Table 8.	Calculated total solar energy transmittance, $g_{total}$ , shading coefficient, (SC), and shading factor, $F_c$ , values of the Gershwin Pty Ltd black mesh screen sample used as external shading in combination with the four standard glazings of EN 13363-1 (11).	11

## I. List of Figures

Figure 1.	Experimental configuration for the measurement of spectral transmittance and reflectance (UV/Vis/NIR) using the PELA 150 integrating sphere reflectance accessory.	3
Figure 2.	Total near-normal hemispherical and near-normal-diffuse spectral transmittance of Nysan Shading Systems sample S01 Superscreen 300 White Pearl.	12
Figure 3.	Total near-normal hemispherical and near-normal-diffuse spectral reflectance (Glazing (F) and Room (B) Sides) of Nysan Shading Systems sample S01 Superscreen 300 White Pearl.	12

# THE OPTICAL PROPERTIES OF A GERSHWIN PTY LTD BLACK MESH SCREEN SAMPLE

## 1. Introduction

The Solar Energy Materials Research Laboratory of Sonnergy Ltd undertakes ultraviolet, visible and infrared spectral optical properties measurements of materials for a wide range of industrial clients. The Laboratory is approved by the Ministry of Defence to perform measurements in compliance with Defence Standard DS0023/1 'NATO Infra Red Reflective (IRR) Green Colour for Painting Military Equipment' (1). The laboratory operates in accordance with ISO 17025 for which compliance is being sought (2). Spectrophotometric instruments are serviced annually by the respective manufacturers. All measurements are made in accordance with recognised international procedures and instruments are calibrated using traceable reference standards. The Laboratory participates regularly in proficiency tests and inter-laboratory comparisons for the measurement of optical properties (3, 4, 5, 7). Sonnergy serves as the Chair of the European Union Cool Roofs Council Technical Committee (6) with responsibility for recommending solar and thermal measurement test procedures for product certification, is a full member of the International Commission on Glass Technical Committee 10 "Optical properties of glass and coated glass products" (7) and provides European representation for the peer review of optical properties spectral data for inclusion in the International Glazing Database (IGDB) (8) administered and maintained by the Lawrence Berkeley National Laboratory, USA.

In this report measurements are presented of the total and diffuse near-normal hemispherical spectral reflectance and transmittance of a black mesh screen sample supplied by Gershwin Pty Ltd, Australia, for the wavelength range 280 – 2500 nm. From these measurements integrated ultraviolet, visible and solar optical properties are calculated in accordance with the international standard procedures of EN 410 (9).

The European Standards EN 14501 and EN 13363-1 (10, 11, 12) are used to calculate values of the total solar energy transmittance,  $g_{total}$ , shading coefficient and shading factor,  $F_c$ , for complex glazing employing the mesh sample in combination with the default glazings of each respective standard. Calculations are performed for the case of the test sample used as an external screen.

## 2. The Gershwin Pty Ltd Sample

The metal mesh screen sample submitted for measurement by Gershwin Pty Ltd, Australia, is identified in Table 1.

Sample No.	Sample Identifier	Sample Colour
S01	Metal Mesh Screen	Black

Table 1. Identification of the Gershwin Pty Ltd sample.

## 3. Experimental procedures

### 3.1. Measurement of Spectral Transmittance and Reflectance

Measurements of near-normal hemispherical spectral transmittance,  $\tau(\lambda)$ , and spectral reflectance,  $\rho(\lambda)$ , were made using a Perkin Elmer Lambda 900 spectrophotometer using the PELA 150 integrating sphere accessory. Measurements were made over the spectral range 280 – 2500 nm (UV/Vis/NIR) to enable calculation of the integrated ultraviolet, visible and solar optical properties.

Total near-normal hemispherical spectral reflectance measurements were made with the sample mounted on the rear sample port of the 0.15 m diameter PELA 150 integrating sphere. The basic experimental configuration is shown in Fig. 1. Calibration was made using 2 Labsphere Spectralon white reflectance standards (13). The measurement procedures were performed in accordance with EN 14500 and CIE 130 (14, 15).

For measurement of the total near-normal hemispherical spectral transmittance,  $\tau_{n-h}(\lambda)$ , the sample is located at the sample entrance port of the integrating sphere (Position A) and the rear sample mounting port (Position B) is covered with a white reflectance standard.

For measurement of the near-normal diffuse spectral transmittance,  $\tau_{n-dif}(\lambda)$ , the sample is located at the sample entrance port of the integrating sphere (Position A) and the rear sample mounting port (Position B) is left open (uncovered) to enable any direct component of the transmitted light to exit the sphere through this port.

For measurement of the total near-normal hemispherical spectral reflectance,  $\rho_{n-h}(\lambda)$ , the sample is located at the rear sample mounting port (Position B) of the integrating sphere and the sample entrance port (Position A) is left open (uncovered).

For measurement of the near-normal diffuse spectral reflectance,  $\rho_{n-dif}(\lambda)$ , the sample is located at the rear sample mounting port (Position B) of the integrating sphere and the integrating sphere specular reflectance exit port cover located at Position C is removed to allow the regularly reflected component to exit the integrating sphere.




Figure 1. Experimental configuration for the measurement of spectral transmittance and reflectance (UV/Vis/NIR) using the PELA 150 integrating sphere reflectance accessory.  
 (D1: Photomultiplier detector; D2: PbS detector)

Each measurement of reflectance and transmittance was performed 4 times with the sample being removed and then replaced inside the spectrophotometer in a different position and the 4 measurements were then averaged.

## 4. Calculation Methods

### 4.1. Visible transmittance and reflectance

The visible transmittance and reflectance of a sample is calculated using the relative spectral power distribution  $D_\lambda$  of illuminant  $D_{65}$  (16) multiplied by the spectral sensitivity of the human eye  $V(\lambda)$  and the spectral bandwidth  $\Delta\lambda$ .

Measurements are made of the spectral transmittance,  $\tau(\lambda)$ , and the visible transmittance,  $\tau_v$ , is then calculated using a weighted ordinate method (9): according to EN 410 using the relationship:

$$\tau_v = \frac{\int_{\lambda=380nm}^{780nm} D_\lambda \tau(\lambda) V(\lambda) d\lambda}{\int_{\lambda=380nm}^{780nm} D_\lambda V(\lambda) d\lambda} = \frac{\sum_{\lambda=380nm}^{780nm} D_\lambda \tau(\lambda) V(\lambda) \Delta\lambda}{\sum_{\lambda=380nm}^{780nm} D_\lambda V(\lambda) \Delta\lambda}$$

Measurements are made of the spectral reflectance  $\rho(\lambda)$ , and the visible reflectance,  $\rho_v$  is also calculated by weighted ordinates according to EN 410 using the relationship:

$$\rho_v = \frac{\int_{\lambda=380nm}^{780nm} D_\lambda \rho(\lambda) V(\lambda) d\lambda}{\int_{\lambda=380nm}^{780nm} D_\lambda V(\lambda) d\lambda} = \frac{\sum_{\lambda=380nm}^{780nm} D_\lambda \rho(\lambda) V(\lambda) \Delta\lambda}{\sum_{\lambda=380nm}^{780nm} D_\lambda V(\lambda) \Delta\lambda}$$

To evaluate these expressions the values of spectral transmittance and reflectance are taken at 10 nm intervals from 380 - 780 nm and the values are normalised since  $\sum D_\lambda V(\lambda) \Delta\lambda = 1$ . The normalised fractional contributions of each interval to the total sum are tabulated in EN 410 (9).

### 4.2. Solar transmittance and reflectance.

The solar transmittance,  $\tau_s$ , is defined (17) as:

$$\tau_s = \frac{\int_{\lambda_1}^{\lambda_2} \tau_\lambda G_\lambda d\lambda}{\int_{\lambda_1}^{\lambda_2} G_\lambda d\lambda}$$

where  $G_\lambda$  is the spectral solar irradiation,  $\tau_\lambda$  is the spectral transmittance and  $\lambda_1$  and  $\lambda_2$  respectively define the short and long wavelength limits of the solar spectral distribution.

The solar absorptance,  $\alpha_s$ , and solar reflectance,  $\rho_s$ , are similarly defined:

$$\alpha_s = \frac{\int_{\lambda_1}^{\lambda_2} \alpha_\lambda G_\lambda d\lambda}{\int_{\lambda_1}^{\lambda_2} G_\lambda d\lambda}$$

$$\rho_s = \frac{\int_{\lambda_1}^{\lambda_2} \rho_\lambda G_\lambda d\lambda}{\int_{\lambda_1}^{\lambda_2} G_\lambda d\lambda}$$

where  $\alpha_\lambda$  and  $\rho_\lambda$  are the spectral absorptance and spectral reflectance respectively.

It is normal only to measure  $\rho_\lambda$  and  $\tau_\lambda$  and to deduce  $\alpha_\lambda$  from the conservation relationship  $\alpha_\lambda + \rho_\lambda + \tau_\lambda = 1$ .

To evaluate the integrals the recommended procedure of EN 410 (9) is used and a weighted ordinate method is employed. Each of the integrals reduces to the form

$$\tau_s = \sum_{i=1}^n \tau_{\lambda_i} f_i \quad \rho_s = \sum_{i=1}^n \rho_{\lambda_i} f_i \quad \alpha_s = \sum_{i=1}^n \alpha_{\lambda_i} f_i$$

where the family  $f_i$  are the relative proportions of the total solar energy in each equal wavelength interval and their sum is normalised to unity.

### 4.3. Ultraviolet Transmittance

The ultraviolet transmittance,  $\tau_{uv}$ , is calculated as (9)

$$\tau_{uv} = \frac{\sum_{\lambda=280nm}^{380nm} U_\lambda \tau_\lambda \Delta\lambda}{\sum_{\lambda=280nm}^{380nm} U_\lambda \Delta\lambda}$$

where  $\tau_\lambda$  is the spectral transmittance,  $U_\lambda$  is the relative distribution of the ultraviolet part of the global solar radiation and  $\Delta\lambda$  is the wavelength interval (5 nm).

#### 4.4. Total solar energy transmittance, shading coefficient and shading factor

Window and glazing thermal performance is described in relation to thermophysical properties denoting energy gains and losses. For the characterization of the energetical performance of a window the three main areas of interest are the determination of the heat transfer through the window, the solar gain through the window, and the light distribution behind the window. The quantitative properties are the overall heat loss coefficient (U-value), the total solar energy transmittance, which is termed the g value, and the visible light transmittance ( $\tau_v$ ).

The total solar energy transmittance, g, is the measure of the total energy passing through the glazing when exposed to solar radiation. It is the sum of the solar transmittance,  $\tau_s$ , and the secondary internal heat transfer factor  $q_i$ , i.e.  $g = \tau_s + q_i$ , the latter term arising from absorption of solar radiation in the glazing and subsequent re-radiation at thermal wavelengths to both the outside and the inside of the enclosure. The g-value is also called the Solar Heat Gain Coefficient (SHGC) and the Solar Factor.

The g value may be calculated for single or multiple glazings from the spectral transmittance and reflectance data and from knowledge of the heat resistances and surface heat transfer coefficients. A simplified method for the calculation of the g-value for glazings employing solar protection devices, such as blinds, is described in EN 13363-1 (11, 12). This method is also recommended when performing calculations in accordance with EN 14501 (10).

For a blind used internally, i.e. placed on the room side of the glazing, the total solar energy transmittance of the glazing-blind configuration,  $g_{total}$ , is calculated from

$$g_{total} = g (1 - g \rho_{sb} - \alpha_{sb} (\Lambda / \Lambda_2))$$

where

- g is the total solar energy transmittance of the glazing without the blind
- $\rho_{sb}$  is the solar reflectance of the blind facing the glazing
- $\alpha_{sb}$  is the solar absorptance of the blind facing the glazing

$\Lambda$  represents the effective heat transfer through the configuration defined as

$$\Lambda = 1 / ((1/U) + (1/\Lambda_2))$$

where U is the heat loss coefficient of the glazing without the blind and  $\Lambda_2$  assumes the value  $18 \text{ W m}^{-2} \text{ }^\circ\text{C}^{-1}$ .

The shading coefficient is derived by comparing the total solar energy transmittance of the glazing with a clear float glass having a total solar energy transmittance of 0.87. This corresponds to float glass of thickness 3-4 mm. The shading coefficient is the total solar energy transmittance, g, divided by 0.87.

The  $g_{total}$  and SC values of the glazing/blind configuration are normally calculated for the blind in combination with default glazing cases. The two European standards EN 14501 (10) and EN 13363-1 (11) each identify 4 reference glazings.

The 4 reference glazings which represent the default cases defined in EN 14501 (12) together with their respective  $g$  and  $U$  values are shown in Table 2.

The 4 reference glazings which represent the default cases defined in EN 1363-1 (13) together with their respective  $g$  and  $U$  values are shown in Table 3.

The Shading Factor,  $F_c$ , is defined (17) as the ratio of the total solar energy transmittance of the glazing-blind assembly,  $g_{total}$ , to the total solar energy transmittance,  $g$ , of the glazing alone, i.e.

$$F_c = \frac{g_{total}}{g}$$

$F_c$  is sometimes also termed  $z$ .

Note that for any given blind, the value of  $F_c$  is dependent upon the glazing with which the blind is combined, i.e. there is not a unique value of  $F_c$  for a given blind product.

<b>Glazing</b>	<b>Thermal transmittance U (<math>W m^{-2} \text{ } ^\circ C^{-1}</math>)</b>	<b>Total solar energy transmittance, g</b>
Single clear glass	5.8	0.85
Double clear glass	2.9	0.76
Solar Control 1	1.2	0.59
Solar Control 2	1.1	0.32

Table 2. Values of the glazing thermal transmittance,  $U$ , and total solar energy transmittance,  $g$ , used to calculate the  $g_{total}$  and shading coefficient values for the blind fabrics placed internally (taken from EN 14501 (10)).

<b>Glazing</b>	<b>Thermal transmittance, U (<math>W m^{-2} \text{ } ^\circ C^{-1}</math>)</b>	<b>Total solar energy transmittance, g</b>
Single clear glass	5.7	0.85
Double clear glass	3.0	0.75
Triple clear glass	2.0	0.65
Double clear glass with low E coating	1.6	0.72

Table 3. Values of the glazing thermal transmittance,  $U$ , and total solar energy transmittance,  $g$ , used to calculate the  $g_{total}$  and shading coefficient values for the blind fabrics placed internally (taken from EN-13363-1 (11)).

For the blind used externally, i.e. placed on the outside of the glazing, the total solar energy transmittance of the glazing-blind configuration,  $g_{total}$ , is calculated from

$$g_{total} = \tau_{sb} g + \alpha_{sb} (\Lambda / \Lambda_2) + \tau_{sb} (1 - g) (\Lambda / \Lambda_1)$$

where

$g$  is the total solar energy transmittance of the glazing without the blind

$\tau_{sb}$  is the solar transmittance of the blind

$\alpha_{sb}$  is the solar absorptance of the blind

$\Lambda$  represents the effective heat transfer through the configuration defined as

$$\Lambda = 1 / ((1/U) + (1/\Lambda_1) + (1/\Lambda_2))$$

where

$U$  is the heat loss coefficient of the glazing without the blind,

$\Lambda_1 = 8 \text{ W m}^{-2} \text{ }^\circ\text{C}^{-1}$  and  $\Lambda_2 = 18 \text{ W m}^{-2} \text{ }^\circ\text{C}^{-1}$ .

## 5. Results

The measured UV/Vis/NIR (300 – 2500 nm) total near-normal hemispherical and near-normal-diffuse spectral transmittance of the Gershwin Pty Ltd black mesh screen sample are shown in Figure 2.

The measured UV/Vis/NIR (300 – 2500 nm) total near-normal hemispherical and near-normal-diffuse spectral reflectance of the Gershwin Pty Ltd black mesh screen sample are shown in Figure 3. For the reflectance measurements, the two sides of the sample are indistinguishable.

From these data, and using the expressions and methods described in Section 4, the respective total near-normal hemispherical solar and visible reflectance, transmittance and absorptance were calculated. These results together with the ultraviolet transmittance are presented in Table 4.

The integrated total near-normal hemispherical, near-normal diffuse and normal-direct solar and visible transmittance values of the Gershwin Pty Ltd black mesh screen sample are shown in Table 5. The normal-direct transmittance values were obtained by subtracting the measured diffuse transmittance from the measured total transmittance.

The integrated total near-normal hemispherical and near-normal diffuse solar and visible reflectance of the Gershwin Pty Ltd black mesh screen sample are given in Table 6. The diffuse reflectance values are found to agree with the corresponding total reflectance.

The estimated uncertainty of all ultraviolet, visible and solar values is + 0.02.

Total solar energy transmittance,  $g_{total}$ , shading coefficient, SC, and shading factor,  $F_c$ , values were calculated for the Gershwin Pty Ltd black mesh screen sample in combination with the reference glazings of the two European standards EN 13363-1 (11) and EN 14501 (10), using the simplified methods described in EN 13363-1.

For the case of the sample deployed as an external screen, calculated total solar energy transmittance (solar heat gain coefficient)  $g_{total}$  values using the EN 14501 reference glazings are presented in Table 7 and for the EN 13363-1 reference glazings in Table 8 respectively.

			Solar Reflectance	Visible Reflectance	Solar Transmittance	Visible Transmittance	Solar Absorptance	Visible Absorptance	Ultraviolet Transmittance
Sample No.	Sample Name	Sample Colour	$\rho_s$	$\rho_v$	$\tau_s$	$\tau_v$	$\alpha_s$	$\alpha_v$	$\tau_{uv}$
S01	Metal Mesh Screen	Black	0.02	0.02	0.43	0.43	0.55	0.55	0.43

Table 4. Integrated total near-normal hemispherical solar, visible and ultraviolet optical properties of the Gershwin Pty Ltd black mesh screen sample.

			Total Solar Transmittance	Total Visible Transmittance	Diffuse Solar Transmittance	Diffuse Visible Transmittance	Direct Solar Transmittance	Direct Visible Transmittance
Sample No.	Sample Name	Sample Colour	$\tau_s$	$\tau_v$	$\tau_{s,d}$	$\tau_{v,d}$	$\tau_{s,n-n}$	$\tau_{v,n-n}$
S01	Metal Mesh Screen	Black	0.43	0.43	0.02	0.02	0.41	0.41

Table 5. Integrated total near-normal hemispherical, near-normal diffuse and normal-direct solar and visible transmittance of the Gershwin Pty Ltd black mesh screen sample.

			Total Solar Reflectance	Total Visible Reflectance	Diffuse Solar Reflectance	Diffuse Visible Reflectance	Direct Solar Reflectance	Direct Visible Reflectance
Sample No.	Sample Name	Sample Colour	$\rho_s$	$\rho_v$	$\rho_{s,d}$	$\rho_{v,d}$	$\rho_{s,n-n}$	$\rho_{v,n-n}$
S01	Metal Mesh Screen	Black	0.02	0.02	0.02	0.02	0.00	0.00

Table 6. Integrated total near-normal hemispherical, near-normal diffuse and normal-direct solar and visible reflectance of the Gershwin Pty Ltd black mesh screen sample.

Fabric Code	Single Clear Glass (A)			Double Clear Glass (B)			Solar Control 1 (C)			Solar Control 2 (D)		
	Total Solar Energy Trans	Shading Coeff	Shading Factor	Total Solar Energy Trans	Shading Coeff	Shading Factor	Total Solar Energy Trans	Shading Coeff	Shading Factor	Total Solar Energy Trans	Shading Coeff	Shading Factor
	g <sub>tot</sub>	SC	F <sub>c</sub>									
S01 Metal Mesh Screen Black	0.47	0.54	0.56	0.41	0.48	0.63	0.31	0.36	0.53	0.21	0.24	0.65

Table 7. Calculated total solar energy transmittance,  $g_{total}$ , shading coefficient, (SC), and shading factor,  $F_c$ , values of the Gershwin Pty Ltd black mesh screen sample used as external shading in combination with the four standard glazings of EN 14501 (10).

Fabric Code	Single Clear Glass			Double Clear Glass			Triple Clear Glass			Double Clear low-e		
	Total Solar Energy Trans	Shading Coeff	Shading Factor	Total Solar Energy Trans	Shading Coeff	Shading Factor	Total Solar Energy Trans	Shading Coeff	Shading Factor	Total Solar Energy Trans	Shading Coeff	Shading Factor
	g <sub>tot</sub>	SC	F <sub>c</sub>									
S01 Metal Mesh Screen Black	0.47	0.54	0.56	0.41	0.47	0.63	0.36	0.41	0.55	0.37	0.43	0.52

Table 8. Calculated total solar energy transmittance,  $g_{total}$ , shading coefficient, (SC), and shading factor,  $F_c$ , values of the Gershwin Pty Ltd black mesh screen sample used as external shading in combination with the four standard glazings of EN 13363-1 (11).




Figure 2. Total near-normal hemispherical and near-normal-diffuse spectral transmittance of Nysan Shading Systems sample S01 Superscreen 300 White Pearl.




Figure 3. Total near-normal hemispherical and near-normal-diffuse spectral reflectance (Glazing (F) and Room (B) Sides) of Nysan Shading Systems sample S01 Superscreen 300 White Pearl.

## 6. References

1. Defence Standard 00-23/Issue 1, 'NATO Infra Red Reflective (IRR) Green Colour for Painting Military Equipment', Ministry of Defence, 17 October 1980.
2. ISO/IEC 17025, General requirements for the competence of testing and calibration laboratories, ISO 2005.
3. WinDat, EU Window Energy Data Network, Contract NNE5-2000-122 Document N2.06 "UV/Vis/NIR Spectrophotometric Near-Normal Specular Transmittance and Reflectance Measurement Intercomparison, Hutchins M G and Kilbey N, [www.windat.org](http://www.windat.org), 2004.
4. Hutchins M G et al, ADOPT, Measurement and prediction of angle dependent optical properties of coated glass products: results of an inter-laboratory comparison of spectral transmittance and reflectance, ICCG-3, Proc. International Conference on Coatings on Glass, Maastricht, 2000, 467-478, Thin Solid Films 392, 269-275, 2001.
5. Thermes, EU Thermal emissivity of energy saving coatings on glass, Contract G6RD-CT-2001-00658, Hutchins M G, Kilbey N and Nijnatten P A van, Thin Solid Films 502 (2006) 164-169.
6. European Union Cool Roofs Council (EU-CRC), <http://coolroofs-eu-crc.eu> .
7. International Commission on Glass Technical Committee 10 "Optical properties of glass and coated glass products", [www.icg-tc10.org](http://www.icg-tc10.org) .
8. International Glazing Database (<http://windows.lbl.gov/materials/IGDB/>), Lawrence Berkeley National Laboratory, USA.
9. BS EN 410 *Glass in Building – Determination of luminous and solar characteristics of glazing*, 1998.
10. EN 14501, Blinds and shutters – Thermal and visual comfort – Performance characteristics and classification, 2005.
11. EN 13363-1, Solar Energy and Light Transmittance through Glazing with Solar Protection Devices – Part 1, Simplified Calculation Method, BSI , Milton Keynes, 2003.
12. Design for improved solar shading control, CIBSE TM37, ISBN-10: 1-903287-57-X, The Chartered Institution of Building Services Engineers London, April 2006.
13. Certificate Reference SRS-99-020-WS-3(NIST), OC73C-3184, Labsphere Inc., USA, Date of Calibration 8 February 2008.
14. EN 14500, Blinds and shutters – Thermal and visual comfort – Test and calculation methods, BSI, 2008.
15. CIE 130-1998, 'Practical methods for the measurement of reflectance and transmittance', 1998.
16. Publication CIE No. 15.2, 'Colorimetry' (second edition), Vienna 1986.
17. Duffie J A and Beckman W A, Solar Engineering of Thermal Processes, 2<sup>nd</sup> Edition, Wiley 1991.

# **S**ONNERGY LTD

*Solar Energy Materials Research Laboratory  
Surface Coatings Testing Service*

**PO Box 489,  
Abingdon,  
Oxon,  
OX14 4WY  
United Kingdom  
Tel: +44 (0) 7733 333429  
Fax: +44 (0) 1235 848684  
E-mail: [sonnergy@sonnergy.com](mailto:sonnergy@sonnergy.com)**